

PolyTerra™

PolyTerra™ is a bioplastic based 3d printing filament designed from the ground up to create the next generation of PLA, providing ease of use, printing quality, speed and reliability.

Physical Properties

Property	Testing method	Typical value
Density	ASTM D792 (ISO 1183, GB/T 1033)	1.31±0.02 (g/cm ³ at 21.5°C)
Glass transition temperature	DSC, 10 °C/min	60.6 (°C)
Vicat Softening temperature	ASTM D1525 (ISO 306 GB/T 1633)	62.7±0.1 (°C)
Melt index	210 °C, 2.16 kg	14-20 (g/10 min)
Melting temperature	DSC, 10 °C/min	162.6 (°C)

Tested with 3D printed specimen of 100% infill

Mechanical Properties


Property	Testing method	Typical value
Young's modulus (X-Y)	ASTM D638 (ISO 527, GB/T 1040)	1882 ± 141 (MPa)
Tensile strength (X-Y)	ASTM D638 (ISO 527, GB/T 1040)	20.9 ± 2.0 (MPa)
Elongation at break (X-Y)	ASTM D638 (ISO 527, GB/T 1040)	34.5 ± 8.1 (%)
Bending modulus	ASTMD790 (ISO 178, GB/T 9341)	2695± 541 (MPa)
Bending strength	ASTMD790 (ISO 178, GB/T 9341)	39.6 ± 1.1 (MPa)
Charpy impact strength	ASTM D256 (ISO 179, GB/T 1043)	5.7± 0.4 (kJ/m ²)
Tensile strength (Z)	ASTM D638 (ISO 527, GB/T 1040)	18.0± 0.3(MPa)
Young's modulus (Z)	ASTM D638 (ISO 527, GB/T 1040)	1869.7 ±38 (MPa)
Elongation at break (Z)	ASTM D638 (ISO 527, GB/T 1040)	2.51 ± 0.83 (%)

All testing specimens were printed under the following conditions:
 nozzle temperature = 200 °C, printing speed = 50 mm/s, build plate temperature = 60 °C, infill = 100%
 All specimens were conditioned at room temperature for 24h prior to testing



Recommended printing conditions

Parameter	
Nozzle temperature	190 - 230 (°C)
Build Surface material	BuildTak®, Glass, Blue Tape
Build surface treatment	Glue, Magigoo
Build plate temperature	25 - 60 (°C)
Cooling fan	Turned on
Printing speed	30-70 (mm/s)
Raft separation distance	0.2 (mm)
Retraction distance	1 (mm)
Retraction speed	20 (mm/s)
Recommended environmental temperature	Room temperature - 60 (°C)
Threshold overhang angle	60 (°)
Recommended support material	PolySupport™ and PolyDissolve™ S1



Based on 0.4 mm nozzle and Simplify 3D v.4.0. Printing conditions may vary with different nozzle diameters




Tensile testing specimen; ASTM D638 (ISO 527, GB/T 1040)



Flexural testing specimen; ASTM D790 (ISO 178, GB/T 9341)



Impact testing specimen; ASTM D256 (ISO 179, GB/T 1043)



Disclaimer:

The typical values presented in this data sheet are intended for reference and comparison purposes only. They should not be used for design specifications or quality control purposes. Actual values may vary significantly with printing conditions. End- use performance of printed parts depends not only on materials, but also on part design, environmental conditions, printing conditions, etc. Product specifications are subject to change without notice.

Each user is responsible for determining the safety, lawfulness, technical suitability, and disposal/recycling practices of Polymaker materials for the intended application. Polymaker makes no warranty of any kind, unless announced separately, to the fitness for any use or application. Polymaker shall not be made liable for any damage, injury or loss induced from the use of Polymaker materials in any application.